


Note. The YA-R3F, a compact manipulator with a motor of 80 W or less mounted on all axes, requires minimal space (baseplate: 240 mm × 170 mm). No fence is required for robot's working area. The robot can be used in applications such as automated guided vehicles (AGVs), testing equipment, and educational tools. Note. Standard models include four air hoses (diameter: 4 mm), and an internal user I/O wiring harness (0.2 mm² × 10) running through the U-arm. This structure simplifies wiring

and tubing for easier system construction. Note. Floor-mounted, wall-mounted, and ceiling-mounted types are available. Please contact us separately regarding wall-mounted or ceiling-mounted installations. Note. This unit can also be used in combination with a travel axis or other external axis. Please contact us.

Controlled Axis		6	
Payload		3 kg	
Repeatability		±0.03 mm	
Range of Motion	S-axis (turning)	-160° to +160° Note 1	
	L-axis (lower Arm)	-85° to +90°	i
	U-axis (upper arm)	-105° to +260°	(
	R-axis (wrist roll)	-170° to +170°	ľ
	B-axis (wrist pich/yaw)	-120° to +120°	
	T-axis (wrist twist)	-360° to +360°	
Maximum Speed	S-axis (turning)	3.49 rad/s, 200°/s	
	L-axis (lower Arm)	2.62 rad/s, 150°/s	(
	U-axis (upper arm)	3.32 rad/s, 190°/s	
	R-axis (wrist roll)	5.24 rad/s, 300°/s	
	B-axis (wrist pich/yaw)	5.24 rad/s, 300°/s	F
	T-axis (wrist twist)	7.33 rad/s, 420°/s	N

Allowable Moment	R-axis (wrist roll)	5.39 N·m	
	B-axis (wrist pich/yaw)	5.39 N·m	
	T-axis (wrist twist)	2.94 N·m	
Allowable Inertia (GD ² /4)	R-axis (wrist roll)	0.1 kg·m ²	
	B-axis (wrist pich/yaw)	0.1 kg·m ²	
	T-axis (wrist twist)	0.03 kg·m ²	
Mass		27 kg	
Ambient Conditions	Temperature	0 to +40°C	
	Humidity	20 to 80%RH (non-condensing)	
	Vibration	4.9 m/s ² or less	
	Others	Free from corrosive gasses or liquids, or explosive gasses Free from exposure to water, oil, or dust Free from excessive electrical noise (plasma)	
Power Requirements ^{Note 2}		0.5 kVA	

Note 1. For wall-mounted installation, the S-axis operating range is $\pm 25^{\circ}$. Note 2. Varies in accordance with applications and motion patterns. Note. SI units are used for specifications.



X